



All MTA Receptacle: Nylon, Tin Plated, 2.54 mm (167)

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #6-1879640-6
H4P 26K1 0.5% 50PPM



TE Part #1-499786-2
064 UNIV HDR RA 4S 15DP STD L1



TE Part #3-1879635-8
H4 787K 0.5% 15PPM



TE Part #1-223969-0
UNV PWR MDL, GUIDE PIN LOCT PL



TE Part #YDTS20W25-04BAV001
RECP ASSY



TE Part #1625980-6
HSX25 R22 5%



TE Part #103968-7
2X8 MTE RCPT SR RIBBED .100CL



TE Part #1-1879519-1
CRGH2010 1% 137R 1W



TE Part #2176050-3
RLP73M 1E R062 5% 5K RL



TE Part #YDTS24W17-06PAC001
RECP ASSY

Documents

Product Drawings

03P MTA100 CONN ASSY BLU LF

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-641655-3_J.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-641655-3_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-641655-3_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English