

Product Details

A205 Stainless Steel Stud and Base

Materials Base - Pressed Stainless Steel type 303 with inset Nitrile Rubber Core with Stainless Steel Tag
 Stud - Stainless Steel type 303



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Overall Height H (mm)	Hole Diameter d (mm)	Maximum Recommended Load (kg)
A205/001	M16	100	75	133	13	750
A205/002	M16	150	75	183	13	750
A205/003	M16	200	75	233	13	750
A205/005	M20	150	75	183	13	750
A205/006	M20	200	75	233	13	750
A205/007	M16	100	100	138	13	1000
A205/008	M16	150	100	188	13	1000
A205/009	M16	250	100	238	13	1000
A205/011	M20	150	100	191	13	1000
A205/012	M20	200	100	241	13	1000
A205/013	M24	150	100	193	13	1000
A205/014	M24	200	100	293	13	1000

Dimensions are approximate

7° ARTICULATION

