

Act: Elec, Mod, 0-10 VDC, NSR, 24 VAC, 200 N, Linear, IP43

8455052000

EAN Code: 3606489659059

Main

Product or component type	Actuator
Actuator type	Electric
Actuator product series	MZ20
Actuator model	MZ20
Product destination	zone valves
Hold-in power consumption in VA	1 VA AC
Power loss return	Non-spring return
Control signal	Proportional/modulating
Targeted region	Europe Asia Pacific. Australia.

Complementary

Actuator	Linear	
control type	Automatic reset	
rated supply voltage	24 V AC	
Analogue input range	010 V DC	
Stroke length	5.5 mm	
Stroke auto calibration	False	
Force N	200 N	
Force lbf	45 lbf	
Position indicator	Stem position cut out on yoke	
Lead length	1.5 m	
Connection valve	Coupling ring M30 x 1.5	
Stroke running time	117 s	

Environment

IP degree of protection	IP43	
Ambient air temperature for operation	-555 °C	
Relative humidity	595 % non-condensing	
Ambient air temperature for storage	-2565 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12 cm
Package 1 Width	9.4 cm
Package 1 Length	8 cm
Package 1 Weight	260 a

Logistical informations

Country of origin SI

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration

Use Again

4 Jul 2025

○ Repack and remanufacture		
Take-back	No	