

Technical data sheet

Article number:
156-03537

FNT1635LOK01SET

Product Group	FastNTube
Material	Polyamide 6.6 recycled, high impact modified, UV-stabilised (PA66HIRUV(REC))
Colour	Grey RAL 7035 (RAL7035)
Bundle Ø max.	35 mm
Bundle Ø min.	16 mm
Cable Tie	Polyamide 6 recycled (PA6(REC100))
Fixation Method	Fir Tree
Flammability	UL 94 HB
Length (L)	175.5 mm
Min.Tensile Strength	320 N
Package Content packed in	box
Pack Cont.	100 pcs.
ROHS compliant	Yes
Variant	Inside Serrated
Width (W)	7.5 mm

