

Lawn Mower XGT®

LM004G

40Vmax, 430 mm

Model LM004G is a 430mm (17") lawn mower powered by 1 x XGT® Li-Ion battery.

Features and Benefits: Cutting, Collecting, Mulching, High mowing performance, Warning lamp for battery capacity, high temperature and overload, Deck material plastic.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3800 min ⁻¹
Cutting height positions	8
Width of Mowing Deck	43 cm
Mowing Height	20 - 75 mm
Rear Wheel Diameter	16,5 cm
Front Wheel Diameter	14 cm
Actual mowing area 8,0 Ah	830 m ²
Cumulative	✓
Bio cutting	✓
Continuous Use XGT® 40V Max / 8.0 Ah	53 min
Collecting Box Capacity	50 L
Sound Power Level (L _{WA})	92 dB(A)

User benefits

- 3 in 1 (Mowing / Grass collecting / Mulching)
- Height adjustment with one handle
- Ergonomic soft grip handle provides increased comfort
- Electric brake for maximum productivity and increased operator safety
- IPX4 rating, splash proof
- Soft start for smooth start-ups
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

■ Optional AC

1913H6-4

Mulching Blade 430 Set



■ Other

User manual

Parts drawing