



MALE END VIEW



SPECIFICATIONS

HOUSING MATERIAL/COLOR	POLYAMIDE/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/FINISH	ALUMINUM/BLACK-ANODIZED
O-RING MATERIAL	BUNA-N
RATED CURRENT [A]	UP to 8.0 A
RATED VOLTAGE [V]	600 V
WIRE SIZE RATING [AWG]	16-22 AWG
CABLE DIAMETER RANGE	5-13mm
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	IP67
TERMINATION TYPE	SCREW TERMINALS



**NOTE
PRELIMINARY
SPECIFICATIONS**

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
1.			ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	RDS	DATE	01/18/11
2.				DSGN		SCALE	1=1.0
3.		MATERIAL		UNIT OF MEASUREMENT		IDENTIFICATION NO.	
4.		SEE SPECIFICATIONS		MILLIMETER [INCH]		REV	
FINISH		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		U2-18536	
SEE SPECIFICATIONS						P2	
SEE SPECIFICATIONS						FILE: U2-18536 SHEET 1 OF 1	

P2	ADD TERMINATION TYPE	CK	03/23/11	34628
REV	DESCRIPTION	BY	DATE	ECO NO.