



64971 - OT K9 C200W 240V R7S 117MM GE BX1/10MIC

Specifications

General characteristics:

Wattage [W]	200
Voltage [V]	240
Lumens [lm]	4000
Rated Lumens per Watt (Efficacy) [lm/W]	20
Cap/Base	R7s
Bulb Shape	Tubular
Bulb Diameter [mm]	8
Colour temperature [K]	3000
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	1000
Dimming Capability	Yes
Coil type	CC-8
Maximum Overall Length [mm]	119
DUN Code	10043168649718
EAN Code	0043168649711
Net weight per piece [g]	7
Gross weight per piece [g]	15
Pack Quantity	10
Inner pack type	BOX
Outer pack type	OUTER BOX
Layer quantity EUR (PC)	1200
Layer quantity UK (PC)	1600
Pallet quantity EUR (PC)	4800
Pallet quantity UK (PC)	6400
Outer case size	127 x 93 x 40 (mm)
Energy Efficiency Class	D
Brand	General Electric (GE)
Product status	Available