

Plastic label - UC-EMLP (60X15) SR - 0828088

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic label, Sheet, silver, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Adhesive, Lettering field: 60 x 15 mm



Why buy this product

- ✓ The UC-EMLP ... UniCard labeling range includes self-adhesive device markers with good adhesive properties
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The sheets provide space for including function texts



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 471367
Weight per Piece (excluding packing)	10.9 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	60 mm
Width (a)	15 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	silver
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA

Plastic label - UC-EMLP (60X15) SR - 0828088

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	4
Number of individual labels per row	1
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27149129

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER, for accommodating UC-EMP..., UC-EMLP...

