


Features

- ANSI MC96.1
- Fast response, welded exposed junction
- Bare Tails termination

RS PRO PFA insulated ANSI Exposed Junction Thermocouple with Bare Tails - Type K

RS Stock No.: 0652761



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Exposed junction thermocouples are often used in applications where fast response times are crucial, such as in research laboratories, semiconductor manufacturing, and certain industrial processes.

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-75°C to 250°C
Construction	Fast response, welded exposed junction
Measuring Junction	Exposed
Standards Met	ANSI
Application	Fast response, welded exposed junction

Mechanical Specifications

Termination	Bare Wire
Length	0.3m (0.98ft)
Cable Insulation	7/0.2mm Teflon® PFA insulated twin-twisted lead

Approvals

Declarations	RoHS
--------------	------

Similar Products

Colour Code	Type	Style	Cable Size	Length	Termination	RS Stock#
ANSI	K	PFA T/T	1/0.2mm	0.3m (0.98ft)	Bare Tails	0652751
ANSI	K	PFA T/T	1/0.2mm	1m (3.3ft)	Bare Tails	8479669
ANSI	K	PFA T/T	1/0.2mm	2m (6.56ft)	Bare Tails	8479665
ANSI	K	PFA T/T	1/0.2mm	2m (6.56ft)	Bare Tails	2623221 (x10)
ANSI	K	PFA T/T	1/0.2mm	5m (16.4 ft)	Bare Tails	8479697
ANSI	K	PFA T/T	1/0.2mm	10m (32.8ft)	Bare Tails	8479735
ANSI	K	PFA T/T	1/0.3mm	0.3m (0.98ft)	Bare Tails	0652759
ANSI	K	PFA T/T	1/0.3mm	1m (3.3ft)	Bare Tails	8479678
ANSI	K	PFA T/T	1/0.3mm	2m (6.56ft)	Bare Tails	8479671
ANSI	K	PFA T/T	1/0.3mm	5m (16.4 ft)	Bare Tails	8479707
ANSI	K	PFA T/T	1/0.3mm	10m (32.8ft)	Bare Tails	8479738
ANSI	K	PFA T/T	7/0.2mm	0.3m (0.98ft)	Bare Tails	0652761
ANSI	K	PFA T/T	7/0.2mm	1m (3.3ft)	Bare Tails	8479690
ANSI	K	PFA T/T	7/0.2mm	2m (6.56ft)	Bare Tails	8479693
ANSI	K	PFA T/T	7/0.2mm	5m (16.4 ft)	Bare Tails	8479713
ANSI	K	PFA T/T	7/0.2mm	10m (32.8ft)	Bare Tails	8479744
ANSI	T	PFA T/T	1/0.3mm	0.3m (0.98ft)	Bare Tails	0652753
ANSI	T	PFA T/T	1/0.3mm	1m (3.3ft)	Bare Tails	8479681
ANSI	T	PFA T/T	1/0.3mm	2m (6.56ft)	Bare Tails	8479687
ANSI	T	PFA T/T	1/0.3mm	2m (6.56ft)	Bare Tails	2623222 (x10)
ANSI	T	PFA T/T	1/0.3mm	3m (9.84ft)	Bare Tails	2318480
ANSI	T	PFA T/T	1/0.3mm	5m (16.4 ft)	Bare Tails	8479704
ANSI	T	PFA T/T	1/0.3mm	10m (32.8ft)	Bare Tails	8479741