

4









3

2

1

© 2025 TE Connectivity. All Rights Reserved.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A		RELEASED PER ECN-25-322737	21MAY2025	TR RCG



A	B	C	D
38.7	36.0	7.9	32.7

Item	Description	Q'TY	Material
1	Shell	1 SET	ABS Black
2	Screws	2 PCS	Iron Alloy Nickel Plating
3	Screws	2 PCS	Iron Alloy Nickel Plating
4	Nut	2 PCS	Iron Alloy Nickel Plating
5	Screws	2 PCS	Iron Alloy Nickel Plating
6	Wire Clamp	2 PCS	Iron Alloy Nickel Plating
7	Shims	2 PCS	Iron Alloy Nickel Plating

CABLE DIAMETERS 6.0~10.0MM.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN TARUN.R 02MAY2025	TE Connectivity
CHK NAIR, SREEKUMAR 03MAY2025	
APVD RAGHAVAN, CG 03MAY2025	
PRODUCT SPEC 108-161904	
APPLICATION SPEC 114-161403	
WEIGHT -	
CUSTOMER DRAWING	

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	± -	1 PLC	± 0.40
2 PLC	± 0.25	3 PLC	± -
4 PLC	± -	ANGLES:	± -
MATERIAL -		FINISH -	

NAME D-SUB 15P BACKSHELL	SIZE A2	CAGE CODE 00779	DRAWING NO. C=2508217	RESTRICTED TO -
SCALE 1:1		SHEET 1 of 1		REV A