

Features

- Robust panel mounting design
- Solder bucket termination
- Silver-plated brass contact for enhanced conductivity
- Nickel-plated brass fixing nut
- Polypropylene insulating body

RS PRO Panel Mount Socket

RS Stock No.: 1806653



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO 4 mm panel mounting socket designed for secure electrical connections in test, measurement and low-voltage electronic applications.

General Specifications

Product Type	Panel Mount Socket
Socket Size	4 mm
Mounting Type	Panel Mount
Termination Type	Solder Bucket
Material	Brass, Silver Plated
Body Material	Polypropylene
Operating Temperature	-20°C to +147°C
Colour	Red
Contact Resistance	10 mΩ

Mechanical Specifications

Length	28.5mm
Body Diameter	11.7mm
Thread Diameter	9.8mm
Panel Cut-out Diameter	8.2mm
Terminal Diameter	4mm

Electrical Specifications

Rated current	10 A
Rated Voltage	50 V
Nominal Working Voltage	250 V RMS

Dimentional Drawing

