



185-16

E0845092

Cable Lug KRF, 185mm2, M16



Product Properties:

| | |
|----------------------------------|----------------------------------|
| Suitable for Class 5 conductor | Yes |
| Suitable for Class 6 conductor | Yes |
| Insulated | No |
| Max. current (I _{max}) | 440 A |
| Number of mounting holes | 1 . |
| Flange shape | Ring shape |
| Colour insulation | Other |
| Slender flange model | No |
| With sight-hole | Yes |
| Conductor category | Several |
| Max Temp | 150 °C |
| Surface protection | Tinned |
| Material | Copper |
| Connecting angle | 180° (horizontal) |
| Series | KRF/KSF (10-500mm ²) |

Dimensions:

| | |
|----|-------|
| HS | 17 mm |
| ID | 21 mm |
| OD | 27 mm |
| T | 6 mm |
| P1 | 17 mm |

| | |
|--------------------------------|---------------------|
| P2 | 20 mm |
| L | 85 mm |
| N | 31 mm |
| W | 39 mm |
| MOQ | 25 . |
| Unit | pcs |
| Bolt dimension (metric) | 16 . |
| Nominal cross section | 185 mm ² |
| Series | KRF/KSF (10-500mm2) |

Approvals:

| | |
|-----------------------------------|-----|
| Approved according to CE | Yes |
| Approved according to UKCA | Ja |
| Approved according to DNV | Yes |

Compliance:

| | |
|--------------------------|-------------------------------|
| Conflict Minerals | Contain "Tin" |
| Extended Minerals | Contain "Copper" |
| PFAS | No PFAS |
| REACH | No SVHC (Latest. 05 Nov 2025) |
| RoHS | RoHS 3 (2015/863) |
| SCIP | Not Applicable |

Other information:

| | |
|---------------------------|---|
| ETIM-Class | EC001051 - Tube cable lug for copper conductors |
| ETIM-Release | 9.0 |
| Trademark | NEMIQ |
| Product Group | Cable lugs |
| Search Description | EFO2024V |
| Alternative SKU | 185-16 |
| E-no | E0845092 |

Logistic information:

| | |
|--------------------------|--|
| Barcode | 733117611997 |
| Country of origin | CN |
| E-no | E0845092 |
| Item status | Stock item, normally in stock with reservation for in between sales. |
| MOQ | 25 . |
| Stock code | 185-16 |
| Taric code | 85369010 |
| Unit | pcs |

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se