



Flexible handle

504



Product no. **13061024**
GTIN **4018754238545**
Model **504-2K/24**



Label. 1/2 Flexible handle L.610mm

Properties.

- with 2-component handle
- Chrome Alloy Steel, chrome-plated
- DIN 3122 / ISO 3315

Benefits.

Made in Germany - STAHLWILLE flexible handle, swivelling 1/2" square drive, non-slip 2-component handle, length 610 mm, DIN 3122/ISO 3315, 13061024.

The ball lock ensures a firm and secure fit of the tools.

Ideal for loosening jammed screws - e.g., wheel nuts and axle bolts on cars and trucks.

Manufactured from high-quality Chrome Alloy Steel with a chromium-plated, corrosion-resistant finish for durability.

Technical attributes.

External square drive (inch)	1/2
DIN	DIN 3122 / ISO 3315
Size	24
Length mm (L)	610 mm

Logistics data.

Depth mm (IFS)	615
Width mm (IFS)	40
Height mm (IFS)	30
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	620
Width (packaged, mm)	45
Height (packaging, mm)	35
Volume (packaged, dm3)	0.9765 dm3
Product no.	13061024
Weight (gross, kg)	1,035

Weight PAP (kg)	0,000
Weight PVC (kg)	0,000
GTIN	4018754238545
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	1
Weight (g)	1051 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
13061015	504-2K/15N	1/2 Flexible handle L.397mm	4018754238521
13061018	504-2K/18N	1/2 Flexible handle L.469mm	4018754238538
13061024	504-2K/24	1/2 Flexible handle L.610mm	4018754238545

GTIN.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal