

53604

Tube Brush, 310 mm, Hard, Red



This is used to clean small spaces between machine parts. Also used for cleaning drainage holes of sinks. The short handle allows the operator to exert pressure.

Technical Data

Item Number	53604
Visible bristle length	5 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	4080 Pcs
Quantity Per Layer (Pallet)	150 Pcs.
Box Length	320 mm
Box Width	285 mm
Box Height	55 mm
Product Diameter	15 mm
Length	310 mm
Width	22 mm
Height	22 mm
Gross Weight	0,058 kg
Net Weight	0,047 kg
Cubik metre	0,0002 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020536045
GTIN-14 Number (Box quantity)	15705020536042
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact