


Item no.: 862-1552  
 Product description: 4-CONDUCTOR DEVICE CONNECTORS FOR TOP FIXING SCREWS AND NUTS 3 MM Ø OR FOR SELF-TAPPING SCREW 2.9 MM Ø L1-N WITH 2x PIN 2 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 500 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
pole count	2
Cross section [mm <sup>2</sup> ]	0.5 - 4 mm <sup>2</sup>
Cross section [AWG]	20 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	13.788 g
Color	black
No. of connection Points	8
No. of potentials	2
Height	21.4 mm
Height	0.843 in
Width	24 mm
Width	0.945 in
Depth	35 mm

Depth	1.378 in
Strip length from	10 mm
Strip length to	11 mm
Strip length	0.41 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
862-1552	CSA	154112-1505030	300	20	22-12
862-1552	DNV	E-10423	500	32	4,0
862-1552	ENEC15	143856-01	500	32	0,5-4
862-1552	GL	33242-06HH	500	32	4
862-1552	LR	91/20112(E6)	500	32	4,0
862-1552	LR	91/20112E4	500	32	4
862-1552	UR	E45172	300	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected