

Thick natural rubber, latex glove, when extra protection for heavy duty applications is needed.

- 50% thicker than standard flock lined gloves
- Extremely high resistance to many ketones, salts, detergents, alcohols, alkalies and fats
- Excellent resistance to mechanical hazards plus increased chemical protection
- Chlorinated
- 100% cotton flock lining to help absorb perspiration
- AQL 1.5

Industries

- Construction
- Machinery and Equipment
- Infrastructure Maintenance
- Chemical

Applications

- Maintenance of plant and heavy equipment
- Chemical processing and preparation
- Janitorial use



Previously known as: Extra 87-950

Key Features

- Extra heavy duty black glove
- Heavy duty with 0.73 mm / 29 mils thickness
- 100% cotton flock lining

Vulcanization Chemical Accelerators

- Natural rubber proteins
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards

CE 0493



Specifications

| BRAND STYLE | DESCRIPTION | SIZE | LENGTH | COLO R | PACKAGE |
|------------------|-----------------------|-------------------|------------|--------|---|
| AlphaTec® 87-950 | Natural Latex Rubber, | 7.5, 8, 9, 10, 11 | 325 / 12.8 | Black | <ul style="list-style-type: none"> 1 pair per inner bag, 12 inner bags per master bag; 12 master bags per carton |

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.