

## Features

- Featuring replaceable ceramic tips
- Non-magnetic
- Tough
- Corrosion resistance to most chemicals, salts and acids
- Various tips available

## RS PRO Tweezers

RS Stock No.: 1369736



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*Type 73MZ Ceramic replaceable tip tweezers are suitable to applications which require holding a small component firmly. The Ceramic tips provide the tweezers with outstanding resistance to high temperatures and aggressive environments combined with exceptional hardness.*

## General Specifications

|                   |                                          |
|-------------------|------------------------------------------|
| Category          | Ceramic Replaceable Tip Tweezers         |
| Model Number      | 73MZ.SA.0                                |
| Country of origin | Switzerland                              |
| Tip Style         | 73                                       |
| Tip Type          | straight, fine, pointed, superior finish |

## Electrical Specifications

|          |    |
|----------|----|
| ESD Safe | No |
|----------|----|

## Mechanical Specifications

|                             |                                         |
|-----------------------------|-----------------------------------------|
| Overall Length              | 140.0 (mm)                              |
| Anti-Acid                   | Yes                                     |
| Anti-Magnetic               | Yes                                     |
| Material                    | Anti-Acid/Anti-Magnetic Stainless Steel |
| Tip Material                | White Ceramic                           |
| Full Body coating/finishing | Sandblasted                             |
| Product Height              | 16.0 (mm)                               |
| Product Width               | 9.0 (mm)                                |
| Tip Thickness               | 0.50 (mm)                               |
| Tip Width                   | 0.30 (mm)                               |
| Weight                      | 16.0 (g)                                |