



## Main

Range of product	Canalis
Product or component type	Busbar trunking
Product compatibility	KBB

## Complementary

Device application	Power socket distribution Lighting
Maximum radiated magnetic field	2 pT
[Ue] rated operational voltage	230...400 V
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	690 V
[Ie] rated operational current	25 A at 35 °C
Network frequency	50/60 Hz
[Icw] rated short-time withstand current	0.44 kA
[Ipk] rated peak withstand current	4.4 kA
Thermal stress limit	195 kA <sup>2</sup> .s
THDI	0...15 % 25 A 15...33 % 20 A 33...100 % 16 A
Maximum voltage drop	<0.72 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.67 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.61 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.55 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting mode	By screws
Busbar description	Straight length
Busbar trunking polarity	L + N + PE
Number of circuits	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of tap-off outlets	3
Control type	Communicating
Standards	EN/IEC 61439-6 EN/IEC 60439-2
Width	3100 mm
Depth	51 mm
Height	60 mm
Length	3 m
Colour	White (RAL 9003)
Net weight	2.4 kg
Quantity per set	Set of 6

## Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
IK degree of protection	IK06 conforming to EN/IEC 62262
Ambient air temperature for operation	0...35 °C (100 % of In) 35...40 °C (96 % of In) 40...45 °C (93 % of In) 45...50 °C (89 % of In) 50...55 °C (85 % of In)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------