



RE936-01

- Multiadapter SOP32
- Epoxy fibre-glass 1.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Ni/Au
- Solder stop mask
- Adaption circuit board for SOP32 with 1,27 mm pitch
- Hole spacing 2.54 mm & 1.27 mm
- Solder pads Ø 2.20 mm
- Hole diameter Ø 1.10 mm und Ø 0.35 mm
- Fits on sockets with a distance of 15.24 mm
- Size 41.91 x 19.05 mm