

PRODUCT-DETAILS

316RS4W

316RS4W Wall mounted socket



General Information

Extended Product Type	316RS4W
Product ID	2CMA167155R1000
EAN	7392696671552
Catalog Description	316RS4W Wall mounted socket
Long Description	Surface socket-outlet, earthing sleeve position 4h, rated current 16A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Yellow

Ordering

E-Number (Sweden)	2416530
E-Number (Finland)	2420186
E-Number (Norway)	2416530
EAN	7392696671552
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	99 mm
Product Net Height	170 mm
Product Net Weight	0.37 kg
Mechanical Drawings	9AKK107991A3822

Container Information

Package Level 1 Width	135 mm
Package Level 1 Depth / Length	140 mm
Package Level 1 Height	200 mm
Package Level 1 Gross Weight	0.37 kg
Package Level 1 EAN	7392696671552
Package Level 1 Units	box 1 piece
Package Level 2 Width	800 mm
Package Level 2 Depth / Length	1200 mm
Package Level 2 Height	900 mm
Package Level 2 Gross Weight	84.38 kg
Package Level 2 EAN	7392696071888
Package Level 2 Units	pallet (lift) 174 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1613211
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	25 mm
Cable Entry Position	Cable entry Ø 25mm
Color	Yellow
Connection Type	Screw
Degree of Protection	IP67 IP69
Frequency (f)	50 Hz 60 Hz
Function	Surface socket outlet
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#316RS4W
Mounting Holes	60x148,2
Number of Poles	4
Order Multiple	1 piece
Product Main Type	TRS
Product Name	Wall mounted socket
Protection Type	Watertight
Rated Current (I _n)	16 A
Rated Voltage (U _r)	100 ... 130 V

Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable For	Surface Socket Outlets
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
Installation Manual	2CMC700014C0016
RAL Number	RAL 7012 - Basalt Grey

Classifications

eClass	27440510
UNSPSC	39120000

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	WireClamp0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Surface Socket Outlets

