

### FR50 - Bizflame Work FR Coverall

**Collection:** Bizflame™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizflame Work: 99% Cotton, 1% Carbon Fibre, 350g

**Outer Carton:** 10

#### Product information

This coverall is perfect for the demands of the offshore industry. Constructed with a highly innovative flame-retardant fabric with high visibility reflective tape double stitched for enhanced visibility. Meeting all the required EN standards, features include triple stitched seams, high visibility strips on shoulders, arms and legs, concealed 2-way front brass zip and two front slant chest pockets with concealed brass zips.

#### Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

#### Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 8.6 CAL/CM<sup>2</sup>, ATPV 9.8 CAL/CM<sup>2</sup>)

IEC 61482-2 IEC 61482-1-2 APC 1

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV=13.6 Cal/CM<sup>2</sup> (HAF=82%))



#### Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Hook and loop cuffs for a secure fit
- Action back for extra freedom of movement
- Concealed zip pocket
- Available in sizes from XS to 6XL
- Triple-stitched seams for extra durability
- 10 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays

**FR50 - Bizflame Work FR Coverall**  
**Commodity Code: 6211321000**

**Test House**

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
 Bracetown Business Park  
 D15 YN2P, Ireland  
 Cert No: 2777/13136-03/E00-00

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)  
 Sebenhirtenstrasse 12A  
 1230, Austria  
 Contact: Marion Pfeiler  
 Cert No: 0598

**Wash Care**



**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR50RERXS	Red	43.0	28.0	50.0	1.5200	0.0602	5036108244249	25036108732757
FR50RERS	Red	43.0	28.0	50.0	1.5800	0.0602	5036108167371	25036108625981
FR50RERM	Red	43.0	28.0	50.0	1.6000	0.0602	5036108167364	25036108625974
FR50RERL	Red	43.0	28.0	50.0	1.6300	0.0602	5036108167357	25036108625967
FR50RERXL	Red	43.0	28.0	50.0	1.6900	0.0602	5036108167388	25036108625998
FR50RERXXL	Red	43.0	28.0	55.0	1.7600	0.0662	5036108167395	25036108626001
FR50RERXXXL	Red	43.0	28.0	55.0	1.8900	0.0662	5036108167401	25036108626018
FR50RER4XL	Red	43.0	28.0	55.0	1.9600	0.0662	5036108244263	25036108732771
FR50RER5XL	Red	43.0	28.0	55.0	2.0100	0.0662	5036108298969	25036108788532