


## FEATURES

- **IP66 Rating:** Ensures protection against dust and powerful water jets, making it suitable for outdoor use.
- **Constant Voltage Operation:** Provides stable output voltage for consistent LED performance.
- **Wide Input Voltage Range:** Operates efficiently with input voltages from 200 to 240 V AC.
- **Multiple Dimming Operations:** Compatible with leading edge, PWM, and trailing edge dimming for flexible lighting control.
- **High Driver Current:** Delivers up to 4.16 A, supporting high-power LED configurations.

## RS PRO 100W LED Driver, IP66 Rated

RS Stock No: 642-795



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 100W LED Driver is designed to provide reliable power to LED lighting systems. With a maximum output power of 100 watts and an IP66 rating, it is ideal for both indoor and outdoor applications where durability and performance are essential.

### General Specifications

Dimming Operation	Leading Edge, PWM, Trailing Edge
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	4.16 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	100 W
Output Voltage	24 V

### Protection Category

IP Rating	IP66
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, 3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547
---------------------	---