

Datasheet

RS Pro Terminal Strip, Straight, 12way, 2 Row, 11mm Fixing Centres, 57A, 400 V, length 130.5mm, Black

RS Stock No: **703-3849**



Product Details

RS Pro 12-way terminal block strip in black colour, has screw terminal for easy installation. It has 12 contacts that supports 16 mm² wire size. This terminal block is current rated for 57 A and voltage rating of 400 V. It comes in two rows with 11 mm pitch. This straight terminal measures 130.5 x 25.3 x 23 mm.

Features and Benefits

- 12-way terminal blocks
- Black colour
- Screw termination
- Available in 24, 32, 57 and 76A



ENGLISH

Specifications:

Body Orientation	Straight
Colour	Black
Current Rating	57 A
Depth	16 mm
Dimensions	130.5 x 20.7 x 16 mm
Fixing Centre	11 mm
Length	130.5 mm
Material	PP
Maximum Operating Temperature	+80°C
Number of Contacts	12
Number of Rows	2
Pitch	11 mm
Voltage Rating	400 V
Width	20.7 mm
Wire Size	10 mm ²
Standards Met	BS EN 60998; CE Certified