

PSENrope Grab Wire Switch with E-Stop, Straight, 75m, 1NC/1NO



Housing material:	Aluminium die cast
Product version:	1.0
Approvals:	CE, BG, cCSAus
Number of N/O:	2
Number of N/C:	2
Voltage at AC15:	240 V
Max. current at AC15:	3.0 A
Housing material:	Zn die cast
Max. rope length:	75 m
Width dimension:	282.0 mm
Height dimension:	88.0 mm
Depth dimension:	90.1 mm
Gross weight:	1056 g
Net weight:	939 g
Ambient temperature:	-30 - 80 °C