


Features

- Flexible and durable H05VVH3G1.0- pvc cable
- Fully moulded IEC C14G Plug
- Free end stripped 25mm
- Fully moulded plug for strength and durability
- 2m length

RS PRO 2m Power cable Unterminated to C14G, IEC, 10A 250 V

RS Stock No.: 0285177



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- From RS PRO a high quality and durable power supply cord suitable for various applications. Supplied with fully moulded IEC C14G plug combined with 1mm sq. harmonised cable. These cables have an unterminated end meaning they can be hard wired to any suitable connector or hard wired direct to appliance.

General Specifications

Connector A	Stripped end Outer jacket 25mm inner cores 5mm
Connector B	C14G Male – Straight EN60320-2-2/E
Sheath Colour	Black
Material	PVC
Applications	DIY and home improvements, Maintenance work, Household Entertainment (TVs, Satellite boxes, routers etc.) Industrial machines and equipment Office desks (monitors, computers, phones) Any Electrical device needed to be powered by mains.

Mechanical Specifications

Length	2m
--------	----

Electrical Specifications


Power Cord Rating	10 A - 250V
Visual Inspection	100%
Electrical Test	100%
High pot test wire to wire	3kVac for 2 sec.
Continuity test	25Aac to grounding / 20A to line and neutral
Polarity test	yes
Skin high pot test	6kVac line to skin

Protection Category

	Eu-Directive 2002/96/EC (WEEE)
	Eu-Directive 2003/11/EC (Council Directive 76/769/EEC)
	Eu-Directive 2002/95/EC (RoHS-Compliant)

Approvals

Stripped end	N/A
C14G EN60320-2-2/E	CE, UKCA, ENEC
Cable	Harmonised <HAR>



All Dimensions in mm