

## Deep groove ball bearings S6204-2RSR

### (Series S62..-2RSR)

main dimensions to DIN 625-1, with anti-corrosion protection, lip seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

d	20 mm
D	47 mm
B	14 mm
d1	28,8 mm
D2	41 mm
Da max	41,4 mm
da min	25,6 mm
ra max	1 mm
rmin	1 mm
m	0,103 kg    Mass

$C_r$	10900 N	Basic dynamic load rating, radial
$C_{0r}$	5300 N	Basic static load rating, radial
$C_{ur}$	345 N	Fatigue limit load, radial
$n_G$	9100 1/min	Limiting speed



