

Neodymium shallow pot datasheet

-Internal thread

- Zinc plated body
- With threaded stem
- 80° max operating temp



Product Information

Neodymium shallow pot with internal thread

Product No.	Eclipse Magnetics Product No.	Diameter mm <i>D</i>	Overall Height mm <i>H</i>	Thread	Weight g	Pull force Newtons
1365466	E1018/NEO/RS	10	4.5	M3	2.5	10
1365467	E1019/NEO/RS	13	4.5	M3	4.3	25
1365468	E1020/NEO/RS	16	4.5	M4	6.3	50
1365469	E1021/NEO/RS	20	6	M4	11	70
1365470	E1022/NEO/RS	25	7	M5	21	135
1365471	E1023/NEO/RS	32	7	M6	36	250
1365472	E1024/NEO/RS	40	8	M6	68	390

