









# 5321/5321SC/5322

5321/ 5321SC	mm									
	SL	TR	A	B	C	D	E	F	G	H
DZ5321-0030	300	323.5	-	-	192	224	-	-	-	-
DZ5321-0030SC	300	319.0	-	-	160	192	-	-	192	224
DZ5321-0035	350	373.5	-	-	224	256	-	-	-	-
DZ5321-0035SC	350	369.0	-	-	224	256	-	-	224	256
DZ5321-0040	400	423.5	160	192	288	320	128	160	-	-
DZ5321-0040SC	400	419.0	160	192	256	288	160	192	288	320
DZ5321-0045	450	473.5	160	192	320	352	128	160	-	-
DZ5321-0045SC	450	469.0	192	224	320	352	192	224	352	384
DZ5321-0050	500	523.5	192	224	384	416	160	192	-	-
DZ5321-0050SC	500	519.0	224	256	352	384	224	256	384	416
DZ5321-0055	550	573.5	192	224	416	448	160	192	-	-
DZ5321-0055SC	550	569.0	224	256	416	448	224	256	448	480
DZ5321-0060	600	623.5	256	288	480	512	192	256	-	-
DZ5321-0060SC	600	619.0	256	288	480	512	256	288	480	512
DZ5321-0070	700	723.5	288	320	576	608	256	288	-	-
DZ5321-0070SC	700	719.0	320	352	544	576	320	352	576	608
DZ5321-0080	790	803.5	352	384	672	704	320	352	-	-
DZ5321-0080SC	790	823.0	352	384	640	672	352	384	672	704
DZ5321-0090	900	923.5	448	480	768	800	384	416	-	-
DZ5321-0100	1000	1023.5	480	512	864	896	448	480	-	-
DZ5321-0110	1100	1123.5	544	576	992	1024	480	512	-	-






## 5322



5322	mm							
	SL	TR	A	B	C	D	E	G
DS5322-0030-2	300	342	-	-	192	224	177	-
DS5322-0035-2	350	392	-	-	256	288	227	-
DS5322-0040-2	400	442	160	192	288	320	277	-
DS5322-0045-2	450	492	192	224	352	384	327	-
DS5322-0050-2	500	542	192	224	384	416	377	-
DS5322-0055-2	550	592	224	256	448	480	427	-
DS5322-0060-2	600	642	256	288	480	512	477	238.5
DS5322-0070-2	700	742	320	352	608	640	577	288.5
DS5322-0080-2	790	822	352	384	672	704	677	338.5



- i**
- GB** † All fixings positions must be used to achieve maximum load rating.  
†† Mount slide below drawer centre line.
  - D** † Es sind alle Befestigungspositionen zu verwenden, damit der maximale Lastwert erzielt wird.  
†† Einbau der Schiene unterhalb der Schubladen-Mittellinie.
  - F** † Tous les points de fixation doivent être utilisés pour obtenir la charge maximale.  
†† Monter la glissière sur l'axe du tiroir de celui-ci.
  - I** † Per ottenere il massimo carico nominale, devono essere usate tutte le posizioni di fissaggio.  
†† Montare la guida sulla linea di mezziera del cassetto.
  - E** † Todas las posiciones de fijación deben ser usadas para se conseguir la capacidad máxima de carga.  
†† Monte la guía por debajo de la línea central.



- i**
- GB** † All fixings positions must be used to achieve maximum load rating.
  - D** † Es sind alle Befestigungspositionen zu verwenden, damit der maximale Lastwert erzielt wird.
  - F** † Tous les points de fixation doivent être utilisés pour obtenir la charge maximale.
  - I** † Per ottenere il massimo carico nominale, devono essere usate tutte le posizioni di fissaggio.
  - E** † Todas las posiciones de fijación deben ser usadas para se conseguir la capacidad máxima de carga.