



Main

Range	Thalassa
Application	Outdoor heavy duty
Accessory / separate part category	Enclosure accessory
Product or component type	Ventilated roof
Device application	Multi-purpose
Mounting location	On top of enclosure
Range compatibility	Thalassa Thalassa PHD suitable enclosure
Quantity per set	Set of 1

Complementary

Material	Steel with anti-corrosive coating
Colour	Grey (RAL 7035)
Surface finish	Polyester powder
Fixing mode	By screws and claws (x2) - screw type M6 - roof fixing point location
Corrosion resistance	90...100 % conforming to ISO 12944 C4H
Height	95 mm
Width	750 mm
Depth	620 mm
IP degree of protection	IP55 conforming to IEC 60529

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations