

DCH133NT-XJ

Perforeteur SDS-plus XR 18V Brushless 2.6J



5035048664568

Product Description:

Impact force (E.P.T.A.): 2.6 Wood/concrete/metal Perforation (CPS): 1500-5500 Level
rate (mm): 30/26/13 Vibration rate (m/s²): 14.5 of



Product features and benefits:

- Compact, lightweight and ergonomic design for better comfort and support during extended periods of use
- 3 modes: perforation in concrete, simple drilling in wood and metal (strike stop), light chiseling (rotation stop)
- Brushless motor for more performance and longer life
- Long Low vibration level for extended use
- Electronic clutch for user protection
-

Specifications techniques :

- Drilling Capacity (Metal):

13 mm

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Multi-position side handle (x1)
- TSTAK Box (x1)

DCH133NT-XJ

Perforateur SDS-plus XR 18V Brushless 2.6J



5035048664568

Part of the DCH133NT series

Ref	▲ Title ▼	▲ ▼
DCH133NT-XJ	Perforateur SDS-plus XR 18V Brushless 2.6J	