



SIMATIC ET 200SP HA, bus adapter BA 2XFC, 2x Fast Connect connection for PROFINET

General information		
Product type designation	BA 2xFC	
Interfaces		
Number of PROFINET interfaces	1; 2 ports (switch) FC	
Supports protocol for PROFINET IO		
• Number of FC (FastConnect) connections	2	
Cable length		
— Cu conductors	100 m	
Ambient conditions		
Ambient temperature during operation		
• min.	-40 °C	
• max.	70 °C	
• horizontal installation, min.	-40 °C	
• horizontal installation, max.	70 °C	
• vertical installation, min.	-40 °C	
• vertical installation, max.	60 °C	
Dimensions		
Width	20 mm	
Height	69.5 mm	
Depth	59 mm	
Weights		
Weight, approx.	53 g	
Classifications		
	Version	Classification
eClass	14	27-24-26-92
eClass	12	27-24-26-92
eClass	9.1	27-24-26-92
eClass	9	27-24-26-92
eClass	8	27-24-26-92
eClass	7.1	27-24-26-92
eClass	6	27-24-26-92
ETIM	10	EC002584
ETIM	9	EC002584
ETIM	8	EC002584
ETIM	7	EC002584
Approvals / Certificates		

General Product Approval



[Miscellaneous](#)



[China RoHS](#)



General Product Approval

For use in hazardous locations



[Declaration of Conformity](#)



For use in hazardous locations

Maritime application



[Miscellaneous](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

last modified:

7/3/2025