



M18 FUEL Metal Saw

M18 FMCS-0X

- MILWAUKEE POWERSTATE Brushless Motor provides more power, more run-time, and longer life.
- The MILWAUKEE REDLITHIUM-ION Battery Pack is the most durable pack on the market delivering more run-time, power and longer battery life.
- REDLINK PLUS Electronic Intelligence enables advanced communication between your batteries and tools, allowing for unmatched levels of performance, protection, and productivity.

MODEL VARIANT



INCLUDES

- M18 FMCS-0 (1)
- Blade (1)
- Blade Wrench (1)
- HD Box (1)

Categories: Sawing & Cutting



M18 FMCS-0X

WHAT'S INCLUDED

M18 FMCS-0 (1)

Blade (1)

Blade Wrench (1)

HD Box (1)

PRODUCT SPECIFICATIONS

Battery platform	M18 REDLITHIUM-ION
Voltage (V)	18
FUEL Gauge	Yes
LED Light	Yes
No Load Speed (rpm)	3900
Blade diameter (mm)	150
Bore size (mm)	20
Max. cutting depth in metal pipe (mm)	57
Max. cutting depth in steel (mm)	6.5
Weight with battery pack if applicable (kg)	4.2kg (4.0Ah)