
2102 : Grey Cast Iron Pipe Cutter





Description

Max thickness: 7 mm (210210).
Max thickness: 8 mm (210220).
Hardened chrome-tungsten steel cutting wheels mounted in separate sections that can be added or removed to adapt the maximum and minimum diameters to the pipe to be cut. Can also be fitted with cutting wheels for ductile cast iron.

References

Sku	A pipe "	A pipe mm	L mm	H mm	E maxi mm	No. of wheels	kg
210210	2.1/2 - 6	76 - 150	600	200	7	8	6,550
210220	5 - 12	125 - 300	1000	260	8	9	16,390

