

HPP V4 EI-PFT housing for HIFF inserts



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 545 0032
Specification	HPP V4 EI-PFT housing for HIFF inserts
HARTING eCatalogue	https://harting.com/09455450032

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Easy Install With board locks With integrated seal

Version

Locking type	PushPull
Details	for all HIFF compatible modules

Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	100
Net weight	6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140061156
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466