



Shrinkable markers, "Continuous Tube", thermal transfer

TCGT - 3:1 Commercial Grade

TCGT is a commercial grade 3:1 heatshrink material supplied as a continuous tube and printable on both sides. The supplied accessories allow users to either perforate the tubing at pre-determined lengths (P4000), or fully sever the markers (S4000) whilst printing with the TrakMark DS or TT4000+ printer.

Print with HellermannTyton's premium range of thermal printers and ribbons.

Printers: TrakMark DS, TT4000+, and TT430

Ribbons: TTRC+, TTDTHOUT, TTRW, TT822OUT8

Accessories for TrakMark DS and TT4000+: Perforator (P4000), Cutter (S4000)

Accessories for TT430: Cutter (S430)

Software: TagPrint Pro

Features and Benefits

- Shrink ratio 3:1
- Available in Black, Blue, Red, White, and Yellow
- Cable range from 39mm to 1mm
- Good mechanical strength and resistance to organic solvents and chemicals
- Highly flexible
- Fulfils CSA requirements
- Delivery in convenient storage boxes
- Easy label design with TagPrint Pro



TCGT – 5 colours of printable tube to cover a wide range of diameters.

MATERIAL	Polyolefin, cross-linked (PO-X)
Operating Temperature	-55 °C to +135 °C
Minimum Shrink Temperature	+90 °C
Shrink Ratio	3:1
Recommended Ribbon Type	TTRC+, TTDTHOUT, TTRW, TT822OUT8
Specifications	CSA

RoHS



TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Pack Cont.	Colour	Article-No.
TCGT3-1BK	3.0	1.0	0.60	176 m	Black (BK)	553-30300
TCGT3-1BU	3.0	1.0	0.60	176 m	Blue (BU)	553-30306
TCGT3-1RD	3.0	1.0	0.60	176 m	Red (RD)	553-30302
TCGT3-1WH	3.0	1.0	0.60	176 m	White (WH)	553-30309
TCGT3-1YE	3.0	1.0	0.60	176 m	Yellow (YE)	553-30304
TCGT4.8-1.6BK	4.8	1.6	0.65	110 m	Black (BK)	553-30480
TCGT4.8-1.6BU	4.8	1.6	0.65	110 m	Blue (BU)	553-30486
TCGT4.8-1.6RD	4.8	1.6	0.65	110 m	Red (RD)	553-30482
TCGT4.8-1.6WH	4.8	1.6	0.65	110 m	White (WH)	553-30489
TCGT4.8-1.6YE	4.8	1.6	0.65	110 m	Yellow (YE)	553-30484
TCGT6-2BK	6.0	2.0	0.70	110 m	Black (BK)	553-30600
TCGT6-2BU	6.0	2.0	0.70	110 m	Blue (BU)	553-30606
TCGT6-2RD	6.0	2.0	0.70	110 m	Red (RD)	553-30602
TCGT6-2WH	6.0	2.0	0.70	110 m	White (WH)	553-30609

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.

Shrinkable markers, "Continuous Tube", thermal transfer

TCGT - 3:1 Commercial Grade



TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Pack Cont.	Colour	Article-No.
TCGT6-2YE	6.0	2.0	0.70	110 m	Yellow (YE)	553-30604
TCGT9-3BK	9.0	3.0	0.80	72 m	Black (BK)	553-30900
TCGT9-3BU	9.0	3.0	0.80	72 m	Blue (BU)	553-30906
TCGT9-3RD	9.0	3.0	0.80	72 m	Red (RD)	553-30902
TCGT9-3WH	9.0	3.0	0.80	72 m	White (WH)	553-30909
TCGT9-3YE	9.0	3.0	0.80	72 m	Yellow (YE)	553-30904
TCGT12-4BK	12.0	4.0	0.85	54 m	Black (BK)	553-31200
TCGT12-4BU	12.0	4.0	0.85	54 m	Blue (BU)	553-31206
TCGT12-4RD	12.0	4.0	0.85	54 m	Red (RD)	553-31202
TCGT12-4WH	12.0	4.0	0.85	54 m	White (WH)	553-31209
TCGT12-4YE	12.0	4.0	0.85	54 m	Yellow (YE)	553-31204
TCGT18-6BK	18.0	6.0	1.00	26 m	Black (BK)	553-31800
TCGT18-6BU	18.0	6.0	1.00	26 m	Blue (BU)	553-31806
TCGT18-6RD	18.0	6.0	1.00	26 m	Red (RD)	553-31802
TCGT18-6WH	18.0	6.0	1.00	26 m	White (WH)	553-31809
TCGT18-6YE	18.0	6.0	1.00	26 m	Yellow (YE)	553-31804
TCGT24-8BK	24.0	8.0	1.20	26 m	Black (BK)	553-32400
TCGT24-8BU	24.0	8.0	1.20	26 m	Blue (BU)	553-32406
TCGT24-8RD	24.0	8.0	1.20	26 m	Red (RD)	553-32402
TCGT24-8WH	24.0	8.0	1.20	26 m	White (WH)	553-32409
TCGT24-8YE	24.0	8.0	1.20	26 m	Yellow (YE)	553-32404
TCGT39-13BK	39.0	13.0	1.25	10 m	Black (BK)	553-33903
TCGT39-13BU	39.0	13.0	1.25	10 m	Blue (BU)	553-33902
TCGT39-13RD	39.0	13.0	1.25	10 m	Red (RD)	553-33901
TCGT39-13WH	39.0	13.0	1.25	10 m	White (WH)	553-33909
TCGT39-13YE	39.0	13.0	1.25	10 m	Yellow (YE)	553-33900

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.