

Jigsaw LXT®

DJV182

18V • 800 – 3 500 min⁻¹

Efficient brushless jigsaw with tool-less blade change

An efficient saw with three-stage pendulum action and tool-less blade change. Engine speed can be adjusted between 800 and 3 500 min⁻¹ from a switch to suit the material. A stroke length of 26 mm and cutting capacity of 135 mm in wood and 10 mm in steel.



LXT **BL** **SOFT**
MOTOR NO LOAD

Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Brushless Motor	✓
Strokes per Minute (SPM)	800 - 3500 min ⁻¹
Length of Stroke	26 mm
Max. Cutting Capacity in Wood (90°)	135 mm
Max. Cutting Capacity in Steel (90°)	10 mm
Capacity Aluminium	20 mm
Orbital Action	✓
Tool weight with battery	2,4 - 2,7 kg
Product Dimensions (L x W x H):	266 x 77 x 208 mm
Max. Bevel Range (Left)	0 - 45 °
Vacuum cleaner connection Ø in / out	23 / 28 mm
Vibration Level, Cutting Boards	7,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Boards	1,5 m/s ²
Vibration Level, Cutting Sheet Metal	3,5 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- The rubber coating on the handle ensures a firm working grip
- Tool-less blade change for fast blade installation and removal
- 3 orbital settings
- LED light illuminates the work site
- Built-in dust blower clears the line of cut for greater accuracy
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Optional AC

126331-0

Dust Nozzle Assy Ø 23 / 28 Mm

192547-9

Vacuum Head

193516-3

Parallel Guide

194367-7

Guide rail, 3 000 mm

199140-0

Guide rail, 1 000 mm

415524-7

Anti-splintering device

783202-0

Hex Wrench 4Mm

837639-4

MakPac (2) Inlay

A-86898

Jig Saw Blade Set

B-06292

Jig Saw Blade Set

P-38772

Jig Saw Blade 130 x 0,8 mm

P-47210

Jig Saw Blade 105 x 1 mm



164095-8

Parallel Guide



192557-6

Anti Splinter Guard



193517-1

Guide rail adapter



198885-7

Guide rail joint connector set, 2 pcs



199826-6

Quick-Release Ratcheting Guide Rail



417852-6

Cover Plate



821550-0

Makpac case (2)



A-86309

Jig Saw Blade 132 x 1,25 mm



B-04933

Jig Saw Blade 70 x 1,05 mm



P-05929

Jig Saw Blade 80 x 0,8 mm



P-38788

Jig Saw Blade 79 x 0,8 mm



P-49622

Jig Saw Blade 100 x 1,25 mm



Other

[User manual](#)

[Parts drawing](#)