


Stylish A4 laminator in compact design with WOW colours. Just 3 minutes warm-up time. Suitable for 80-125 microns.





- Brings style to you home office in a range of WOW metallic colours
- Hassle free laminating with excellent results, no complicated settings
- Ready to use in 3 minutes - no more long waits to reach operating temperature
- Low energy consumption, auto shut-off when the device isn't used for 30 minutes
- For 80 to 125 microns
- Takes approximately 60 seconds to laminate one 80 micron A4 sheet
- LED ready lights and audible alert
- Includes free pouches starter kit
- 2 year guarantee, GS / TUV / CE certified
- Recommended for use with Leitz UDT Pouches



Item no.	73680064
Colour	green metallic
Material	ABS plastic
Dimensions (W x H x D mm)	125 x 75 x 370
Laminating Speed	max. 310 mm/min; fixed
Temperature	max. 122° for 80; max 130° for 125u
Power Supply	220/240 V AC
Pre-Heating Time	3 min
Heating System	2 from outside heated rollers
Mode of Operation	2 roller, no carrier, temperature controlled
Max. Laminating Width	230 mm
Max. Laminating Thickness	0.6 mm
Pouch Thickness	80(75)-125 microns
Power Input	285 W
Dimensions (with Tray) mm	370(L)x125(W)x75(H)
Release Mechanism	manual release lever
Approx. lamination time (A4)	60 sec (A4 80 microns)
Photo friendly	√
Guarantee	2 years
Packaging unit	2
Used for	A4 format

Weight (g) 1250
Outer packaging 1
Pallet quantity 72
Minimum order quantity 2
EAN code

4002432112951

 blue metallic	Item no. 73680036
 dark grey	Item no. 73680089
 green metallic	Item no. 73680064
 pink metallic	Item no. 73680023

