

# Eaton 216374

Catalog Number: 216374

Eaton Moeller® series M22 Mounting clamp



## General specifications

Product Name	Catalog Number
Eaton Moeller® series M22 Accessory Mounting clamp	216374
	EAN
	4015082163747
Product Length/Depth	Product Height
10 mm	41 mm
Product Width	Product Weight
30 mm	0.003 kg

## Certifications

UL  
UL 508  
UL Category Control No.: NKCR  
IEC/EN 60947-5  
UL File No.: E29184  
CSA-C22.2 No. 14-05  
CE  
CSA Class No.: 3211-03  
CSA  
CSA File No.: 012528  
CSA-C22.2 No. 94-91

## General

### Type

Mounting clamp (front mounting) for 3-contact LED elements

## Climatic environmental conditions

### Ambient operating temperature - min

-25 °C

### Ambient operating temperature - max

70 °C

### Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

## Actuator

### Connection to SmartWire-DT

Yes

### Connection type

Front fixing

## Cable

### Force for positive opening - min

0 N

## Resources

### Brochures

[RMQ Titan - brochure](#)

[RMQ Small E-Stop - Flyer](#)

[RMQ MCI - Flyer](#)

[RMQ Titan emergency stop push button - Flyer](#)

[RMQ Flat Enclosure - Flyer](#)

### Catalogs

[Flip catalog - Product Range Catalog - Command and indication](#)

[Product Range Catalog Command and Indication Control Circuit Devices, Signal Towers](#)

### Drawings

[eaton-operating-adapter-m22-mounting-clamp-dimensions-002.eps](#)

[eaton-operating-samrtwire-m22-mounting-clamp-3d-drawing.eps](#)

[eaton-operating-adapter-m22-mounting-clamp-flow-diagram.eps](#)

### Installation instructions

[IL04716002Z](#)

### Installation video

[RMQ Flat Design](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All rights reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)