



ENGLISH

Datasheet

## RS Pro SR66 1.55V Silver Oxide Coin Button Battery

RS Stock No: **514-7766**



### Product Details

RS Pro SR66 silver oxide coin button battery is non-rechargeable cell, suitable for use in cameras, clocks, watches and calculators. It features superior discharge characteristics in comparison to alkaline cell and nominal voltage of 1.55 V. This battery is shock, vibration and acceleration resistant.

### Features and Benefits

- Superior discharge characteristics in comparison to alkaline cells
- Good low temperature performance characteristics
- Good resistance to shock, vibration and acceleration
- Low constant internal resistance
- Excellent service maintenance
- Nominal voltage 1.55 V

**Specifications:**

Also Known As	376, SR626SW, SR66, SR626, SB-AW, 280-39, BA V377, D377, 606, S626E, AG4
Brand Range	RS
Chemistry	Silver Oxide
Size	SR66
Terminal Type	Standard
Capacity	25 mAh
Diameter	6.8 mm
Dimensions	6.8 x 2.6 mm
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	-10°C
Nominal Voltage	1.55 V
Operating Temperature Range	-10 to +50°C
Size	SR66
Weight	0.4 g
Typical Application	Cameras, Clocks, Watches, Calculators