

Features

- *Conductor*
Material: 100% copper wires
- *Jacket Material:*
PVC, Black
- *Cable Length:*
0.3M
- *Easy to install and reliable connection*
- *Color: Black*

RS PRO DC Cables

RS Stock No.: 0658293



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Current: 3A.

Voltage: 12V.

*Material: 2*0.5mm² copper wire.*

Polarity distinction: Brown positive, blue negative.

Connector 1: DC 5.5mm x 2.1mm x 9.5mm socket.

Connector 2: bare wire with terminal crimped.

It is for equipment DIY power supply and maintenance replacement, such as LED light strips, CCTV security surveillance camera systems, CCD Camera, wireless camera, or low voltage application systems.

General Specifications

<i>Connector A</i>	<i>Socket DC5.5*2.1mm</i>
<i>Connector A Gender</i>	<i>Female</i>
<i>Connector B</i>	<i>Open, terminal crimped</i>
<i>Connector Style</i>	<i>Socket, Straight</i>
<i>Outer Sheath Material</i>	<i>PVC</i>
<i>Sheath Colour</i>	<i>Brown, blue</i>
<i>Connector Plating</i>	<i>Nickel</i>

Electrical Specifications

<i>Connection</i>	<i>Open end cable</i>
<i>Voltage Rating</i>	<i>12V DC</i>
<i>Maximum Power</i>	<i>3A</i>

Mechanical Specifications

<i>Length</i>	<i>0.3m</i>
<i>Cable Specification</i>	<i>2*0.5mm² copper wire</i>

Operation Environment Specifications

Operating Temperature	0°C to 70°C
Storage Temperature	0°C to 70°C

Approvals

Standards Met	RoHS, Reach
Declarations	RoHS, Reach

