




FAG

6028-2RSR

Deep groove ball bearing

Deep groove ball bearing 60...-2RSR, single row, seals, steel sheet metal cage

Technical information



Your current product variant

Sealing	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	GA13	Ball bearing and insert bearing grease, standard for D>62mm
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	140 mm	Bore diameter
D	210 mm	Outside diameter
B	33 mm	Width
C _r	117,000 N	Basic dynamic load rating, radial
C _{0r}	109,000 N	Basic static load rating, radial
C _{ur}	5,100 N	Fatigue load limit, radial
n _G	1,650 1/min	Limiting speed
≈m	3.51 kg	Weight

Mounting dimensions

d _{a min}	148.8 mm	Minimum diameter shaft shoulder
D _{a max}	201.2 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum fillet radius



Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	187.54 mm	Shoulder diameter outer ring
D ₂	191.28 mm	Caliber diameter outer ring
d ₁	161.85 mm	Shoulder diameter inner ring

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	100 °C	Operating temperature max.

Calculation factors

f ₀	16	Calculation factor
----------------	----	--------------------

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides