

VARTA Magnetic Safety Light 2CR2032 Box



Visibility is safety: With it's compact and lightweight design, IP54, flexible fixing options and different light modes, it is a truly multi-use light source.



Information

- Multi-Use: use for running, pets, backpacks, schoolbags or strollers
- 5 light modes: white (high, low, blinking) and red (high, blinking)
- Water resistant (IP54) and shock proof (2m drop test)
- Flexible fixation via magnet or double carabiner
- With reflective elements to increase visibility
- Compact and lightweight
- 2x CR2032 button cells included

Article Details

Ordernumber	16621 101 121
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	(up to) 5.00 m
Runtime	(up to) 15 h
Total light output	(up to) 25 lm
Product Height mm	45.80

Logistical Data	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 121373	80.00	31.00	195.00	0.08
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 121380	357.00	88.00	85.00	0.43
PAL (Pallet)	1248	40 08496 214754	800.00	1,200.00	1,170.00	153.85
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
12	26		312		4	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.
VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

