



DCS7485T2

54V XR FLEXVOLT Table Saw Kitted

Selling Proposition

- 22 kg unit weight and optimised footprint make this the most portable saw in its class
- Steel roll cage protects saw against jobsite drops and impacts
- Rack and pinion fence system, front and rear fence lock and large, clear scales combine to give an extremely accurate and easy to use saw
- Powerful Brushless 54v motor for high performance in all applications
- Fence system provides 610 mm of rip capacity in a portable design for cutting large sheet materials to size
- Cast table top design ensures accuracy and precision

Standard Equipment

- 24 tooth SERIES 30® saw blade
- Mitre fence
- 2 blade spanners
- Parallel fence
- Dust port reducer

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	- Watts
Power Output	- Watt
Blade Speed	5800 rpm
Blade Diameter	210 mm
Blade Bore	30 mm
Bevel Capacity	-3 to 48 °
Max. Ripping Capacity [right]	610 mm
Max. Ripping Capacity [left]	318 mm