

KarboTECT® 950



APPLICATION

- › metal work and processing
- › large bakeries
- › changing tools at hot machines
- › laboratories, heat ovens and cabinet dryers
- › refineries
- › all areas with dry contact heat

QUALITIES AND ADVANTAGES

- › good thermal insulation
- › high cut resistance
- › good and close fit for exact handling, even with high temperatures
- › high wearing comfort due to wool inlay


HEAT RESISTANT GLOVES



Article no.	950
Name	KarboTECT® 950
Material	para-aramid, carbon, wool
Description	heavy knitted, knit wrist
Length (mm)	240 - 260
Colour	yellow/black
Size	7, 9, 10
Classification	category III
	<small>EN388:2016</small> <small>EN407</small>  1X4XC 4242XX



FEATURES

- › very economic, as gloves are ambidextrous
- › contact heat up to 250 °C
- ›  food safety according to EU 1935/2004

www.kcl.de
sales@kcl.de



by Honeywell

KCL GmbH

Industriepark Rhoen
 Am Kreuzacker 9
 36124 Eichenzell
 Germany
 Phone +49 6659 87-300
 Fax +49 6659 87-318

Honeywell