



### Main

Range of product	Mureva Styl
Product or component type	Cable outlet
Range compatibility	Mureva Styl

### Complementary


Device presentation	Mechanism
Device mounting	Surface Flush
Number of modules	1 module
Number of cables	3
Maximum cable cross section	2.5 mm <sup>2</sup>
Cable entry	Easy valve access
Condition of use	Indoor/outdoor
Colour tint	White (RAL 9003)
Length	71 mm
Height	45 mm
Width	71 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

Quality labels	CE
IP degree of protection	IP55
IK degree of protection	IK08

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes

China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	0