

Drawn cup needle roller bearings with open ends HK1614-RS (Series HK..-RS)

lip seal on one side, to DIN 618

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	16 mm	
D	22 mm	
C	14 mm	Tolerance: 0/-0,3
rmin	0,8 mm	
m	13 g	Mass
Cr	7600 N	Basic dynamic load rating, radial
C0r	9700 N	Basic static load rating, radial
Cur	1180 N	Fatigue limit load, radial
nG Fett	9300 1/min	Limiting speed for grease lubrication
	IR12X16X16-XL	Suitable inner ring

