

# Product data sheet

Specifications



## Easy UPS On-Line SRVS 72V Battery Pack for 2/3KVA Extended Runtime Model

SRVS72BP-9A

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Battery type	Lead-acid battery
Provided equipment	Documentation CD User manual

### Physical

Colour	Black
Height	33.6 cm
Width	19 cm
Depth	42.5 cm
Net weight	38 kg
Mounting mode	Not rack-mountable
USB compatible	No

### Conformance

Product certifications	CE EAC EN/IEC 62040-1
------------------------	-----------------------------

### Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...15000 m

## Batteries & Runtime

Number of battery blocks per string	6
Device mounting	Floor mounted
Number of battery filled slots	0
Number of battery free slots	0
Battery voltage	72 V

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	40.2 kg
Package 1 Height	32.5 cm
Package 1 width	23.5 cm
Package 1 Length	56.5 cm
Unit Type of Package 2	P06
Number of Units in Package 2	1
Package 2 Weight	40.5 kg
Package 2 Height	59 cm
Package 2 width	60 cm
Package 2 Length	80 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------