

## Han TC200 Buchsenkontakt 25mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 11 000 6220  |
| Specification      | Han TC200 Buchsenkontakt 25mm <sup>2</sup>                                    |
| HARTING eCatalogue | <a href="https://harting.com/09110006220">https://harting.com/09110006220</a> |

### Identification

|                 |               |
|-----------------|---------------|
| Category        | Contacts      |
| Series          | TC 200        |
| Type of contact | Crimp contact |

### Version

|                       |                   |
|-----------------------|-------------------|
| Termination method    | Crimp termination |
| Gender                | Female            |
| Manufacturing process | Turned contacts   |

### Technical characteristics

|                         |                    |
|-------------------------|--------------------|
| Conductor cross-section | 25 mm <sup>2</sup> |
| Rated current           | ≤200 A             |
| Contact resistance      | ≤0.3 mΩ            |
| Stripping length        | 19 mm              |
| Limiting temperature    | -40 ... +125 °C    |
| Mating cycles           | ≥500               |

### Material properties

|                     |  |
|---------------------|--|
| Material (contacts) | Copper alloy   |
| Surface (contacts)  | Silver plated  |
| RoHS                | compliant with exemption                               |
| RoHS exemptions     | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status          | compliant with exemption                               |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| China RoHS                           | 50                                   |
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead<br>Nickel                       |

## Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
|----------------|--------------------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 2  |
| Net weight                     | 20 g                                       |
| Country of origin              | Germany                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140015319                              |
| eCl@ss                         | 27440204 Contact for industrial connectors |
| ETIM                           | EC000796                                   |
| UNSPSC 24.0                    | 39121522                                   |