



Current inputs

| | | |
|--------------------------------------|----------|--------|
| Primary current I _{pn} (/5) | A | 600 |
| Operational frequency | min | Hz 50 |
| | max | Hz 60 |
| Secondary output current | A | 5 |
| Overload withstand I _{pn} | % | 120 |
| Burden | cl. 0.5s | VA 2.5 |
| | cl. 0.5 | VA 5 |

Insulations

| | | |
|--|-----------------------|---------|
| Rated insulation voltage U _i IEC/EN | V | 720 |
| IEC rated short-time thermal current I _{th} | I _{th} for s | 40...60 |
| IEC rated dynamic current I _{dyn} | I _{th} for s | 2.5 |
| Insulation dry type | | Class E |

Mechanical features

| | |
|----------------|----------------------|
| Terminals type | Screw |
| Fixing | DIN rail or by Screw |
| Weight | g 480 |

Ambient conditions

| | | | |
|-------------------|-----------------------|------|-----|
| Temperature | Operating temperature | | |
| | min | °C | -25 |
| | max | °C | +50 |
| | Storage temperature | | |
| | min | °C | -40 |
| | max | °C | +80 |
| Relative humidity | % | 90 | |
| Protection degree | | IP30 | |

Certifications and compliance

| | |
|----------------|-------------------|
| Certifications | IEC/EN/BS 61869-1 |
| | IEC/EN/BS 61869-2 |
| Compliance | EAC |

ETIM classification

EC000066 - Power contactor, AC switching