

# Specifications

## Eaton 120HFMA80



### General Specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage oil fuse
<b>CATALOG NUMBER</b>	120HFMA80
<b>PRODUCT LENGTH/DEPTH</b>	254 mm
<b>PRODUCT HEIGHT</b>	63.5 mm
<b>PRODUCT WIDTH</b>	63.5 mm
<b>PRODUCT WEIGHT</b>	1900 g
<b>COMPLIANCES</b>	BS 2692-1 ESI 12-8
<b>CERTIFICATIONS</b>	IEC Rated IEC60282-1
<b>EAN</b>	5027590432702
<b>UPC</b>	051712585484

## Electrical data

AMPERAGE RATING	80 A
VOLTAGE RATING	12 kV
BREAKING CAPACITY	45 kA
PERFORMANCE CAT	
ACCORDING TO IEC 60282-1	Back-up
RATED FREQUENCY - MIN	50 Hz
CLASS	Class back-up
RESISTANCE	10.9

## Product specifications

APPLICATION	protection of primary side transformer, and oil-filled fuse switch combination unit
FUSE INDICATOR	with striker
FUSE SIZE	254 x 63.5 mm
STANDARD	British Standard

## Resources

BROCHURES	<a href="#">eaton-bussmann-circuit-protection-brochures-en.pdf</a>
MCAD MODEL	<a href="#">eaton-mv-oil-fuse-links-mcad-3d-models-12ohfma-71-100a.stp</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

